



TRC270F



Plug adaptor radio, ON/OFF, 10/16A, FRA

Technical properties

Architecture

Bus system RF

Functions

Bus module detachable No

Configuration

Number of modules 0

Controls and indicators

Indicator lamp yes

Main electrical features

Rated operational voltage Ue 195 / 230 / 253 V

Electric current

Number of entry circuits 0

Maximum through current 16 A

Rated current 16 A

Frequency

Transmission frequency 868 MHz

Power

Max. power with electronic transfo. 1200 W

Max. switching power 3680 W

Scope of delivery

Bus connection included No

Equipment

Number of outputs 1

Bidirectional radio frequency Yes

Modular expandability No

Safety

REACH conform No

RoHS conform Yes

Halogen free No