




TU404



4-channel remote control

Technical properties

Architecture

Fixing mode other

Functions

ETS additional functions ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value

Quicklink functions quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Connectivity

Radio protocol KNX Radio

Receiver category 2

Dimensions

Depth of installed product 15.8 mm

Height of installed product 83 mm

Dimensions (LLxwwxhh) 83 x 46,5 x 15,8 mm

Width of installed product 46.5 mm

Frequency

Transmission frequency 868 MHz

Radio transmission frequency 868.3 MHz

Power

Radio transmission power < 10 mW

Battery

Battery service life [years] ≈ 5

Equipment

Number of radio channels 4

Use

Differentiation characteristic 1 - Sales with labelling field

Safety

Protection index IP IP50

Use conditions

Operating temperature -10...45 °C