




TU404



4-channel remote control

Technical properties

Architecture

Fixing mode	other
-------------	-------

Functions

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Function	easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control, reset function (to factory setting)
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Controls and indicators

Button / push-button	with configuration button
----------------------	---------------------------

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Dimensions

Depth of installed product	15.8 mm
Height of installed product	83 mm
Dimensions (LLxwxhh)	83 x 46,5 x 15,8 mm
Width of installed product	46.5 mm

Frequency

Transmission frequency	868 MHz
Radio transmission frequency	868.3 MHz

Power

Radio transmission power	< 10 mW
--------------------------	---------

Battery

Battery service life [years]	≈ 5
------------------------------	-----

LED control

LED	with configuration LED, with transmission status and battery status LED, red/green/orange
-----	---

Connection

Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
----------------	--

Equipment

Subject to technical modifications

Number of radio channels	4
Use	
Differentiation characteristic 1 - Sales	with labelling field
Safety	
Protection index IP	IP50
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-10...45 °C
Energy-saving	low intrinsic energy requirement