



TU406



**6-channel remote control**

**Technical properties**

**Architecture**

Fixing mode other

**Functions**

ETS additional functions ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value

Quicklink functions quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

**Connectivity**

Radio protocol KNX Radio

Receiver category 2

**Dimensions**

Depth of installed product 16 mm

Height of installed product 133.6 mm

Dimensions (LLxwxhh) 133,6 x 50,2 x 16 mm

Width of installed product 50.2 mm

**Frequency**

Transmission frequency 868 MHz

Radio transmission frequency 868.3 MHz

**Power**

Radio transmission power < 10 mW

**Battery**

Battery service life [years] ≈ 5

**Equipment**

Number of radio channels 6

**Use**

Differentiation characteristic 1 - Sales with labelling field

**Safety**

Protection index IP IP30

**Use conditions**

Operating temperature 0...45 °C