



**Partition for steel trunking without C-profile to BRS/LFS/FWKP height 60mm**

**Technical properties**

**Architecture**

Fixing mode Clamping

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility TWS/BRS/BRSN

**Dimensions**

Trunking height 70 mm

Length 2000 mm

**Materials**

Material Steel

Material group steel

Type of surface treatment Galvanised

**Standards**

European directive RoHS voluntary compliance

**Use conditions**

Operating temperature -5...90 °C

TWS70VERZ