



TX460B

Environment control and regulation Tebis Silver

Technical properties

Architecture

Bus system	EIB
Number of keys	4
Fixing mode	section make

Configuration

Static differential	0,5< °C <1
Installation type	hot water radiator, hot water floor heating, electrical radiator, electrical floor heating, fancoil

Voltage

System supply voltage	30V DC via bus
-----------------------	----------------

Electric current

Number of entry circuits	4
--------------------------	---

Dimensions

Dimensions (LLxwwxhh)	BAU : 70.7 x 70.7 x 21.1mm BOF : 80.5 x 80.5 x 15.4mm
-----------------------	---

Measurement

Reduced temperature setting	16°C
-----------------------------	------

Screen

Display	with retro-lighting
---------	---------------------

Materials

Colour	silver
RAL colour	RAL 7031 - Blue grey

Settings

Comfort temperature setpoint	10 / 30 °C
------------------------------	------------

Equipment

With anti-theft/dismantling protection	Yes
With display	yes

Safety

Protection index IP	IP20
Frost protection temperature setting	8 °C

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

temperatur

Standby temperature setpoint	19°C
------------------------------	------