



TXA100



IP20

easy configuration tool kit

Technical properties

Configuration

Category / ports RJ45 Port for LAN connection

Controls and indicators

Manual selection switches / push-buttons Selection switch for online/offline mode

Button / push-button with programming button and red programming LED

Connectivity

Ethernet data rate max. 2 x 100/1000 Mbit/s

Connectors / jacks with 2 USB jacks type B, USB 2.0 compliant

Voltage

Operating voltage 230 V AC

Operating voltage over bus 21...32 V DC

Dimensions

Dimensions (LLxwxh) 41.5x33x10 cm

LED control

LED with green and red status LED for LAN status, operational stand-by, KNX status and gateway connection

Connection

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

Settings

Supported configuration modes easy

Scope of delivery

Bus connection included Yes

Contents of the kit Configuration tool + WIFI access point + Power supply 1x 30VDC + 1x 24VDC

Equipment

Updateable Yes

Visualization No

Web-Server Yes

Software

Software portable case with complete set for commissioning of KNX installations in easy mode

Use conditions

Operating temperature 0...45 °C

Storage/transport temperature -20...70 °C

Identification

Main design line KNX

Instructions

Information text Network technology skills are required for commissioning. System requirements: Windows 8.1, Android 4.4, iOS 8.