



TXA100



IP20

**easy configuration tool kit**

**Technical properties**

**Configuration**

Category / ports RJ45 Port for LAN connection

**Controls and indicators**

Manual selection switches / push-buttons Selection switch for online/offline mode

Button / push-button with programming button and red programming LED

**Connectivity**

Ethernet data rate max. 2 x 100/1000 Mbit/s

Connectors / jacks with 2 USB jacks type B, USB 2.0 compliant

**Voltage**

Operating voltage 230 V AC

Operating voltage over bus 21...32 V DC

**Dimensions**

Dimensions (LLxwxh) 41.5x33x10 cm

**LED control**

LED with green and red status LED for LAN status, operational stand-by, KNX status and gateway connection

**Connection**

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

**Settings**

Supported configuration modes easy

**Scope of delivery**

Bus connection included Yes

Contents of the kit Configuration tool + WIFI access point + Power supply 1x 30VDC + 1x 24VDC

**Equipment**

Updateable Yes

Visualization No

Web-Server Yes

**Software**

Software portable case with complete set for commissioning of KNX installations in easy mode

**Use conditions**

---

Operating temperature 0...45 °C

Storage/transport temperature -20...70 °C

**Identification**

---

Main design line KNX

**Instructions**

---

Information text Network technology skills are required for commissioning. System requirements: Windows 8.1, Android 4.4, iOS 8.