



TXA206C

## Output 6 -fold 16A

### Technical properties

#### Architecture

Bus system EIB

#### Functions

Multi-phase mode suitable to switch different external conductors

#### Configuration

Number of modules 4

#### Controls and indicators

Indicator lamp yes

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Rated current 16 A

#### Voltage

Operating voltage over bus 21...32 V DC

Output voltage 230 V~

System supply voltage 30V DC via bus

#### Electric current

Number of entry circuits 0

Maximum through current 16 A

Rated current 16 A

#### Power

Max. power with electronic transfo. 1200 W

Total power loss under IN 12 W

Output power 2300 W

Max. switching power 8625 W

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 20 x 36 W

#### Incandescent bulbs control

Max. power with incandescent lamps 2300 W

#### Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Type of contacts	6NO
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Type of connection	quick connect
<b>Scope of delivery</b>	
Bus connection included	Yes
<b>Equipment</b>	
Number of outputs	6
Bidirectional radio frequency	No
Modular expandability	No
<b>Use conditions</b>	
Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
<b>Identification</b>	
Main design line	KNX