



TXA206C

Output 6 -fold 16A

Technical properties

Architecture

Bus system EIB

Functions

Multi-phase mode suitable to switch different external conductors

Configuration

Number of modules 4

Controls and indicators

Indicator lamp yes

Main electrical features

Rated operational voltage U_e 230 V

Rated current 16 A

Voltage

Operating voltage over bus 21...32 V DC

Output voltage 230 V~

System supply voltage 30V DC via bus

Electric current

Number of entry circuits 0

Maximum through current 16 A

Rated current 16 A

Power

Max. power with electronic transfo. 1200 W

Total power loss under IN 12 W

Output power 2300 W

Max. switching power 8625 W

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 20 x 36 W

Incandescent bulbs control

Max. power with incandescent lamps 2300 W

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of contacts	6NO
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Type of connection	quick connect
Scope of delivery	
Bus connection included	Yes
Equipment	
Number of outputs	6
Bidirectional radio frequency	No
Modular expandability	No
Use conditions	
Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
Identification	
Main design line	KNX