



TXA210AN

**Dimmer 1 channel 300W**

**Technical properties**

**Architecture**

Bus system KNX

**Configuration**

Number of modules 4

**Controls and indicators**

Indicator lamp yes

**Main electrical features**

Frequency 50/60 Hz

Rated current 1.3 A

**Voltage**

System supply voltage 30V DC via bus

**Power**

Incandescent bulb power 20 / 300 W

Total power loss under IN 2.3 W

Power of the variator 0 / 300 W

**Fluorescent bulbs control**

Power lighting fluo lamps 60W

**LED control**

Power LED 60 W

**Connection**

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Type of load universal

Type of connection quick connect

**Equipment**

Type of dimmer universal

Bidirectional radio frequency No

**Use conditions**

Operating temperature 0...45 °C

Storage/transport temperature -20...70 °C