



TXA210AN

Dimmer 1 channel 300W

Technical properties

Architecture

Bus system	KNX
Fixing mode	Din-Rail

Configuration

Number of modules	4
-------------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Frequency	50/60 Hz
Rated current	1.3 A

Voltage

System supply voltage	30V DC via bus
-----------------------	----------------

Power

Incandescent bulb power	20 / 300 W
Total power loss under IN	2.3 W
Power of the variator	0 / 300 W

Materials

Colour	stone grey
--------	------------

Fluorescent bulbs control

Power lighting fluo lamps	60W
---------------------------	-----

LED control

Power LED	60 W
-----------	------

Connection

Type of load	universal
--------------	-----------

Equipment

Type of dimmer	universal
Bidirectional radio frequency	No

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature

0...45 °C

Storage/transport temperature

-20...70 °C