



TXA210N

Dimmer 1 channel 600W

Technical properties

Architecture

Bus system KNX

Configuration

Number of modules 4

Controls and indicators

Indicator lamp yes

Main electrical features

Rated current 2.6 A

Voltage

System supply voltage 30V DC via bus

Power

Incandescent bulb power 20 / 600 W

Total power loss under IN 4.8 W

Power of the variator 0 / 600 W

Fluorescent bulbs control

Power lighting fluo lamps 120W

LED control

Power LED 120 W

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of load universal

Equipment

Type of dimmer universal

Bidirectional radio frequency No

Use conditions

Operating temperature 0...45 °C

Storage/transport temperature -20...70 °C