



TXA223

Output device for 4 shutters 230V~

Technical properties

Architecture

| | |
|-----------------------------------|-----|
| Bus system | KNX |
| Number of blinds/shutters outputs | 4 |

Functions

| | |
|-----------------------|----|
| Bus module detachable | No |
|-----------------------|----|

Configuration

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Controls and indicators

| | |
|----------------|-----|
| Indicator lamp | yes |
|----------------|-----|

Main electrical features

| | |
|------------------------|----|
| Type of supply voltage | DC |
|------------------------|----|

Voltage

| | |
|-----------------------|----------------|
| System supply voltage | 30V DC via bus |
|-----------------------|----------------|

Electric current

| | |
|---------------------------|-----|
| Number of entry circuits | 0 |
| Maximum switching current | 6 A |

Power

| | |
|----------------------------------|--------|
| Contact rating with 230 V in AC1 | 1380 W |
| Total power loss under IN | 2 W |

Connection

| | |
|---|---------------------------|
| Connection cross-sect. flexible conductor | 0,75 / 2,5mm ² |
| Connection cross-sect. rigid cable | 0,75 / 2,5mm ² |
| Number of contacts | 4 |
| Type of connection | quick connect |

Scope of delivery

| | |
|-------------------------|-----|
| Bus connection included | Yes |
|-------------------------|-----|

Equipment

| | |
|-------------------------------|----|
| Bidirectional radio frequency | No |
|-------------------------------|----|

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | 0...45 °C |
| Storage/transport temperature | -20...70 °C |

