



UC200FU

Perforated Bracket, quadro evo, L200 mm

Technical properties

Dimensions

| | |
|-----------------------------|--------|
| Depth of installed product | 44 mm |
| Height of installed product | 50 mm |
| Width of installed product | 200 mm |
| Built-in height | 50 mm |

Cover, door

| | |
|------------|----------------|
| Cover type | Closed (plain) |
| Cover type | none / closed |

Materials

| | |
|------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
|------------|-----------------------|

Connection

| | |
|--------------------------|---|
| Number of conduit inlets | 0 |
|--------------------------|---|

Equipment

| | |
|---------------------|----|
| Number of rows | 0 |
| Quantity of rails | 0 |
| Can be accessorized | No |
| Extension possible | No |

Standards

| | |
|-------------------------|---------------|
| Approvals | EN 61439-1/-2 |
| European directive WEEE | not concerned |

Safety

| | |
|---|--------------|
| IK protection code against mechanical impacts | 10 |
| Protection class | isol.class I |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |