



UC2080AMD

Adjustable DIN rail,quadro evo 200x800

Technical properties

Dimensions

Depth of installed product	95 mm
Height of installed product	96 mm
Width of installed product	800 mm

Capacity

Quantity of half modules terminales per rail	72
--	----

Installation, mounting

Quantity of terminal steps in 1/2 modules on kit	72
--	----

Equipment

Number of rows	1
Quantity of steps in height	8

Safety

Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	Yes