



UC434XN

**Vertical 1xMCCB kit, quadro evo, H3+ x630, 348x398 mm**

**Technical properties**

**Configuration**

|                   |   |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

**Dimensions**

|                             |        |
|-----------------------------|--------|
| Depth of installed product  | 188 mm |
| Height of installed product | 400 mm |
| Width of installed product  | 350 mm |

**Capacity**

|                                              |   |
|----------------------------------------------|---|
| Quantity of half modules terminales per rail | 0 |
|----------------------------------------------|---|

**Cover, door**

|            |       |
|------------|-------|
| Cover type | Cover |
|------------|-------|

**Materials**

|            |                       |
|------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
|------------|-----------------------|

**Installation, mounting**

|                                                  |   |
|--------------------------------------------------|---|
| Quantity of terminal steps in 1/2 modules on kit | 0 |
|--------------------------------------------------|---|

**Scope of delivery**

|            |     |
|------------|-----|
| With cover | Yes |
|------------|-----|

**Equipment**

|                             |     |
|-----------------------------|-----|
| Number of units             | 1   |
| Number of rows              | 0   |
| Quantity of rails           | 0   |
| Can be accessorized         | Yes |
| Quantity of steps in height | 4   |

**Standards**

|           |               |
|-----------|---------------|
| Approvals | EN 61439-1/-2 |
|-----------|---------------|

**Safety**

|                  |              |
|------------------|--------------|
| Protection class | isol.class I |
| REACH conform    | No           |
| RoHS conform     | Yes          |
| Halogen free     | Yes          |