

Perforated Bracket,quadro evo, L900 mm

Technical properties

Dimensions

Depth of installed product	44 mm
Height of installed product	50 mm
Width of installed product	900 mm
Built-in height	50 mm

Cover, door

Cover type	Closed (plain)
Cover type	none / closed

Connection

Number of conduit inlets	0
--------------------------	---

Equipment

Number of rows	0
Quantity of rails	0
Can be accessorized	No
Extension possible	No

Standards

Approvals	EN 61439-1/-2
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	10
Protection class	isol.class I
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes



UC900FU