



VA24D

**Encl.,Volta,surface,2x12MOD,IP30,Version France**

**Technical properties**

**Architecture**

Fixing mode surface-mounting

**Electric current**

Rated current 63 A

**Dimensions**

Depth of installed product 96.5 mm

Internal depth 92.5 mm

Height of installed product 370 mm

Width of installed product 305 mm

Width in division units 24

Thickness of sidewall material 2.5 mm

**Cover, door**

Type of door closing Latch

Identification of protection index 30

Interlockable No

Cover type With Notch

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

**Settings**

Enclosure type Distributor empty cabinet

**Equipment**

Number of rows 2

Can be accessorized Yes

Number of openings for flange plates 0

Extension possible Yes

Neutral terminal block No

Signal passing door No

**Standards**

GWT Glow wire test	750 °C
European directive WEEE	not concerned
Protection class according to IEC-61140	II

**Safety**

Protection index IP	IP30
Protection class	isol.class II
Impact strength	IK07