



VA24D

Encl.,Volta,surface,2x12MOD,IP30,Version France

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	96.5 mm
Internal depth	92.5 mm
Height of installed product	370 mm
Width of installed product	305 mm
Width in division units	24
Thickness of sidewall material	2.5 mm

Cover, door

Identification of protection index	30
Interlockable	No
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

Equipment

Number of rows	2
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Neutral terminal block	No
Signal passing door	No

Standards

GWT Glow wire test	750 °C
European directive WEEE	not concerned
Protection class according to IEC-61140	II

Safety

Protection index IP	IP30
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07