



VE105U

Enclosure,vector,with emergency stop for heating

Technical properties

Architecture

Fixing mode surface-mounting

Functions

Overvoltage protection No

Configuration

Number of modules 6

Electric current

Rated current 63 A

Dimensions

Insertion depth 0 mm

Depth of installed product 113 mm

Internal depth 150 mm

Height of installed product 190 mm

Width of installed product 165 mm

Width in division units 6

Cover, door

Type of door closing Latch

Identification of protection index 55

Interlockable Yes

Number of keylock of the door 1

Cover type Closed (plain)

Cover type Door

Transparent cover or door Yes

Materials

Colour red

Installation, mounting

Suitable for outdoor use No

Settings

Enclosure type Distributor empty cabinet

Equipment

Number of rows 1

Quantity of rails 1

Can be accessorized	Yes
With bell transformer	No
With socket	No

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP55
Protection class	isol.class II