



VE110L

**Enclosure,vector,IP5x,10 Modules,version Austria**

**Technical properties**

**Architecture**

Fixing mode surface-mounting

**Functions**

With a pipe-in lead Yes

**Configuration**

Number of modules 10

**Main electrical features**

Nominal voltage 400 V

**Electric current**

Rated current 63 A

**Dimensions**

Depth of installed product 114 mm

Internal depth 114 mm

Height of installed product 210 mm

Width of installed product 237 mm

Width in division units 10

Thickness of sidewall material 2.5 mm

**Cover, door**

Type of door closing Latch

Identification od protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour light grey

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment untreated

**Installation, mounting**

Subject to technical modifications

---

Suitable for outdoor use

No

---

**Connection**

Number of conduit inlets

6

---

**Settings**

Enclosure type

Distributor empty cabinet

---

**Equipment**

Number of rows

1

Quantity of section in width

1

Quantity of rails

1

Can be accessorized

Yes

Number of openings for flange plates

20

Extension possible

No

Earthing terminal block

No

Neutral terminal block

No

Signal passing door

Yes

---

**Standards**

GWT Glow wire test

750 °C

European directive WEEE

concerned

---

**Safety**

Protection class

isol.class II

---

**Use conditions**

Operating temperature

-25...40 °C