



VE110L

Enclosure,vector,IP5x,10 Modules,version Austria

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	10
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	114 mm
Internal depth	114 mm
Height of installed product	210 mm
Width of installed product	237 mm
Width in division units	10
Thickness of sidewall material	2.5 mm

Cover, door

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Number of conduit inlets	6
--------------------------	---

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	20
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	Yes

Standards

GWT Glow wire test	750 °C
--------------------	--------

Safety

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
Halogen free	No

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------