



VE412PN

Enclosure,vector,surface mounted,IP65,48M,UV stable,with metric cable entry

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 48

Compatibility

Suitable for Multimedia No

Main electrical features

Nominal voltage 400 V

Voltage

Rated operational voltage in DC 1000 V DC

Electric current

Rated current 63 A

Dimensions

Depth of installed product 151 mm

Internal depth 151 mm

Height of installed product 677 mm

Width of installed product 310 mm

Width in division units 12

Thickness of sidewall material 2.5 mm

Cover, door

Type of door closing Latch

Identification od protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour	light grey
Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Connection

Number of conduit inlets	12
--------------------------	----

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	4
Quantity of section in width	1
Quantity of rails	4
Can be accessorized	Yes
Number of openings for flange plates	46
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection class	isol.class II
Glow wire test	according EN 60695-2-11: 850°C

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------