



VF104PF

Small distributor,golf,flush,1row,4M,IP40,MS-terminal,PE,white door

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	4
-------------------	---

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Insertion depth	72 mm
Depth of wall niche	72 mm
Depth of installed product	97.5 mm
Internal depth	97.5 mm
Height of installed product	225 mm
Installation height	189 mm
Width of installed product	204 mm
Width in division units	4
Built-in height	189 mm
Built-in width	170 mm

Cover, door

Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	white
RAL colour	RAL 9010 - Pure white

Material	plastic
Type of surface treatment	untreated
Installation, mounting	
Suitable for outdoor use	No
Equipment	
Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	Yes
Standards	
GWT Glow wire test	650 °C
European directive WEEE	not concerned
Safety	
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Use conditions	
Operating temperature	-25...40 °C