



VF104TF



**Small distributor,golf,flush,1row,4M,IP40,MS-terminal,PE,transparent door**

## Technical properties

### Architecture

Fixing mode flush-mounting

### Functions

With a pipe-in lead Yes

### Configuration

Number of modules 4

### Main electrical features

Nominal voltage 400 V

### Electric current

Rated current 63 A

### Dimensions

Insertion depth 72 mm

Depth of wall niche 72 mm

Depth of installed product 97.5 mm

Internal depth 97.5 mm

Height of installed product 225 mm

Installation height 189 mm

Width of installed product 204 mm

Width in division units 4

Built-in height 189 mm

Built-in width 170 mm

### Cover, door

Identification of protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

### Materials

Colour white

RAL colour RAL 9010 - Pure white

Material	plastic
Type of surface treatment	untreated
<b>Installation, mounting</b>	
Suitable for outdoor use	No
<b>Equipment</b>	
Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	Yes
<b>Standards</b>	
GWT Glow wire test	650 °C
European directive WEEE	not concerned
<b>Safety</b>	
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Operating temperature	-25...40 °C