



VF312TJ



**Small distributor,golf,flush,3row,36M,IP40,MS-terminal,N+PE,transparent door**

## Technical properties

### Architecture

Fixing mode	flush-mounting
-------------	----------------

### Functions

With a pipe-in lead	Yes
---------------------	-----

### Configuration

Number of modules	36
-------------------	----

### Main electrical features

Nominal voltage	400 V
-----------------	-------

### Electric current

Rated current	63 A
---------------	------

### Dimensions

Insertion depth	72 mm
Depth of wall niche	72 mm
Depth of installed product	97.5 mm
Internal depth	97.5 mm
Height of installed product	543 mm
Installation height	507 mm
Width of installed product	352 mm
Width in division units	12
Built-in height	507 mm
Built-in width	318 mm

### Cover, door

Identification od protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

### Materials

Colour	white
RAL colour	RAL 9010 - Pure white

Material	plastic
Type of surface treatment	untreated
<b>Installation, mounting</b>	
Suitable for outdoor use	No
<b>Equipment</b>	
Number of rows	3
Quantity of section in width	1
Quantity of rails	3
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes
<b>Standards</b>	
GWT Glow wire test	650 °C
European directive WEEE	concerned
<b>Safety</b>	
IK protection code against mechanical impacts	IK07
Protection index IP	IP40
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	Yes
<b>Use conditions</b>	
Operating temperature	-25...40 °C