



VF318PJ

Small distributor,golf,flush,3row,54M,IP40,MS-terminal,N+PE,white door

Technical properties

Functions

With a pipe-in lead Yes

Configuration

Number of modules 54

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 63 A

Dimensions

Insertion depth 72 mm

Depth of wall niche 72 mm

Depth of installed product 97.5 mm

Internal depth 97.5 mm

Height of installed product 543 mm

Installation height 507 mm

Width of installed product 460 mm

Width in division units 18

Built-in height 507 mm

Built-in width 426 mm

Cover, door

Identification of protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	3
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	3
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	0
--------------------------------------	---

Extension possible	Yes
--------------------	-----

Earthing terminal block	Yes
-------------------------	-----

Neutral terminal block	Yes
------------------------	-----

Signal passing door	Yes
---------------------	-----

Standards

GWT Glow wire test	650 °C
--------------------	--------

Safety

IK protection code against mechanical impacts	07
---	----

Protection class	isol.class II
------------------	---------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------