




VS118TF



**Small distributor,golf,surface,1row,IP40,18M,MS-terminal,PE,transparent door**

## Technical properties

### Architecture

Fixing mode surface-mounting

### Functions

With a pipe-in lead Yes

### Configuration

Number of modules 18

### Main electrical features

Nominal voltage 400 V

### Electric current

Rated current 63 A

### Dimensions

Depth of installed product 99 mm

Internal depth 99 mm

Height of installed product 252 mm

Width of installed product 390 mm

Width in division units 18

### Cover, door

Identification od protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

### Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

### Installation, mounting

Suitable for outdoor use No

**Equipment**

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	Yes

**Standards**

GWT Glow wire test	650 °C
European directive WEEE	not concerned

**Safety**

IK protection code against mechanical impacts	07
Protection index IP	IP40
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------