



VS122TF

Small distributor,golf,surface,1row,IP40,22M,MS-terminal,PE,transparent door

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	22
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	99 mm
----------------------------	-------

Internal depth	99 mm
----------------	-------

Height of installed product	252 mm
-----------------------------	--------

Width of installed product	462 mm
----------------------------	--------

Width in division units	22
-------------------------	----

Cover, door

Identification od protection index	40
------------------------------------	----

Interlockable	No
---------------	----

Number of keylock of the door	0
-------------------------------	---

Cover type	Closed (plain)
------------	----------------

Door locking	without
--------------	---------

Door leave	single
------------	--------

Cover type	Door
------------	------

Transparent cover or door	Yes
---------------------------	-----

Materials

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	plastic
----------	---------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

Standards

GWT Glow wire test	650 °C
European directive WEEE	not concerned

Safety

Protection index IP	IP40
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------