



VS312TF



**Small distributor,golf,surface,3row,IP40,36M,MS-terminal,PE,transparent door**

**Technical properties**

**Functions**

With a pipe-in lead Yes

**Configuration**

Number of modules 36

**Main electrical features**

Nominal voltage 400 V

**Electric current**

Rated current 63 A

**Dimensions**

Depth of installed product 99 mm

Internal depth 99 mm

Height of installed product 500 mm

Width of installed product 282 mm

Width in division units 12

**Cover, door**

Identification of protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

**Installation, mounting**

Suitable for outdoor use No

**Settings**

Enclosure type Distributor empty cabinet

**Equipment**

Number of rows	3
Quantity of section in width	1
Quantity of rails	3
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	Yes

**Standards**

GWT Glow wire test	650 °C
European directive WEEE	not concerned

**Safety**

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------