



VS318PJ

Small distributor,golf,surface,3row,IP40,54M,MS-terminal,N+PE,white door

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 54

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 63 A

Dimensions

Depth of installed product 99 mm

Internal depth 99 mm

Height of installed product 500 mm

Width of installed product 390 mm

Width in division units 18

Cover, door

Type of door closing Latch

Identification od protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

Installation, mounting

Subject to technical modifications

Suitable for outdoor use

No

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	3
Quantity of section in width	1
Quantity of rails	3
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

Standards

GWT Glow wire test	650 °C
European directive WEEE	concerned

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP40
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------