



VS318TF



Small distributor,golf,surface,3row,IP40,54M,MS-terminal,PE,transparent door

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 54

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 63 A

Dimensions

Depth of installed product 99 mm

Internal depth 99 mm

Height of installed product 500 mm

Width of installed product 390 mm

Width in division units 18

Cover, door

Type of door closing Latch

Identification od protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

Installation, mounting

Subject to technical modifications

Suitable for outdoor use

No

Settings

Enclosure type Distributor empty cabinet

Equipment

Number of rows 3

Quantity of section in width 1

Quantity of rails 3

Can be accessorized Yes

Number of openings for flange plates 0

Extension possible Yes

Earthing terminal block Yes

Neutral terminal block No

Signal passing door Yes

Standards

GWT Glow wire test 650 °C

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 07

Protection index IP IP40

Protection class isol.class II

REACH conform No

RoHS conform Yes

Halogen free No

Use conditions

Operating temperature -25...40 °C