



VS318TJ

**Small distributor,golf,surface,3row,IP40,54M,MS-terminal,N+PE,transparent door**

**Technical properties**

**Architecture**

Fixing mode surface-mounting

**Functions**

With a pipe-in lead Yes

**Configuration**

Number of modules 54

**Main electrical features**

Nominal voltage 400 V

**Electric current**

Rated current 63 A

**Dimensions**

Depth of installed product 99 mm

Internal depth 99 mm

Height of installed product 500 mm

Width of installed product 390 mm

Width in division units 18

**Cover, door**

Type of door closing Latch

Identification od protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

**Installation, mounting**

Subject to technical modifications

Suitable for outdoor use

No

### Settings

Enclosure type Distributor empty cabinet

### Equipment

Number of rows 3

Quantity of section in width 1

Quantity of rails 3

Can be accessorized Yes

Number of openings for flange plates 0

Extension possible Yes

Earthing terminal block Yes

Neutral terminal block Yes

Signal passing door Yes

### Standards

GWT Glow wire test 650 °C

European directive WEEE concerned

### Safety

IK protection code against mechanical impacts 07

Protection index IP IP40

Protection class isol.class II

REACH conform No

RoHS conform Yes

Halogen free No

### Use conditions

Operating temperature -25...40 °C