



VS418TJ

Small distributor,golf,surface,4row,IP40,72M,MS-terminal,N+PE,transparent door

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	72
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	99 mm
Internal depth	99 mm
Height of installed product	647 mm
Width of installed product	390 mm
Width in division units	18

Cover, door

Identification od protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	4
Quantity of section in width	1
Quantity of rails	4
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

Standards

GWT Glow wire test	650 °C
European directive WEEE	concerned

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP40
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------