



VZ020D

Pressure balance screw joint,vector,IP66, M20

Technical properties

Dimensions

Screw head size in mm	27 mm
thread length	8 mm

Materials

Colour	light grey
Material	plastic
Material quality	thermoplastic
Type of surface treatment	untreated

Connection

Clamping range	6-13 mm
----------------	---------

Cable

Cable Ø	6...13 mm
---------	-----------

Equipment

Screened	No
----------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------