



VZ025D

**Pressure balance screw joint,vector,IP66, M25**

**Technical properties**

**Dimensions**

Screw head size in mm	32 mm
thread length	8 mm

**Materials**

Colour	light grey
Material	plastic
Material quality	thermoplastic
Type of surface treatment	untreated

**Connection**

Clamping range	9-17 mm
----------------	---------

**Cable**

Cable Ø	11...17 mm
---------	------------

**Equipment**

Screened	No
----------	----

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------