



VZ032D

Pressure balance screw joint,vector,IP66,M32

Technical properties

Dimensions

Screw head size in mm	41 mm
thread length	9 mm

Materials

Colour	light grey
Material	plastic
Type of surface treatment	untreated

Connection

Clamping range	13-21 mm
----------------	----------

Cable

Cable Ø	9...17 mm
---------	-----------

Equipment

Screened	No
----------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------