



VZ040M

Cable gland, vector, IP65, M40, plastic

Technical properties

Dimensions

Screw head size in mm	46 mm
thread length	10 mm

Materials

Colour	light grey
Material	Polyamid (PA)
Type of surface treatment	untreated

Connection

Clamping range	19-28 mm
----------------	----------

Cable

Cable Ø	19...28 mm
---------	------------

Equipment

Screened	No
----------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-20...100 °C
-----------------------	--------------