



VZ040M

Cable gland, vector, IP65, M40, plastic

Technical properties

Dimensions

Screw head size in mm	46 mm
thread length	10 mm

Materials

Colour	light grey
Material	Polyamid (PA)
Material quality	thermoplastic
Type of surface treatment	untreated

Connection

Clamping range	19-28 mm
----------------	----------

Cable

Cable Ø	19...28 mm
---------	------------

Equipment

Screened	No
----------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection index IP	IP65
---------------------	------

Use conditions

Operating temperature	-20...100 °C
-----------------------	--------------