



VZ040M

**Cable gland, vector, IP65, M40, plastic**

**Technical properties**

**Dimensions**

Screw head size in mm	46 mm
thread length	10 mm

**Materials**

Colour	light grey
Material quality	thermoplastic
Type of surface treatment	untreated

**Connection**

Clamping range	19-28 mm
----------------	----------

**Cable**

Cable Ø	19...28 mm
---------	------------

**Equipment**

Screened	No
----------	----

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-20...100 °C
-----------------------	--------------