



VZ133N

Door, Volta, flush/Hollow wall, transparent, 3 rows

Technical properties

Architecture

| | |
|------------------------|---------|
| Intended door position | left |
| Fixing mode | Screwed |

Compatibility

| | |
|-----------------------------|-----------------------------|
| Suitable for enclosure type | Hollow wall ; Flush mounted |
|-----------------------------|-----------------------------|

Dimensions

| | |
|-----------------------------|----------|
| Depth of installed product | 36 mm |
| Height of installed product | 570.5 mm |
| Width of installed product | 288 mm |
| Built-in height | 570.5 mm |
| Built-in width | 288 mm |

Cover, door

| | |
|-----------------------------------|-----------|
| Material thickness cover | 1 mm |
| Type of door closing | Latch |
| Number of keylock of the door | 0 |
| Door type for switch gear cabinet | Stop door |
| Door leave | single |
| Transparent cover or door | Yes |

Materials

| | |
|---------------------------|-----------------------|
| Colour | white |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | plastic |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|--------------------------|----|
| Suitable for outdoor use | No |
|--------------------------|----|

Equipment

| | |
|----------------|---|
| Number of rows | 3 |
|----------------|---|

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP30 |
|---------------------|------|