



VZ134N

**Door, Volta, flush/Hollow wall, transparent, 4 rows**

**Technical properties**

**Architecture**

Intended door position	left
Fixing mode	Screwed

**Compatibility**

Suitable for enclosure type	Hollow wall ; Flush mounted
-----------------------------	-----------------------------

**Dimensions**

Depth of installed product	36 mm
Height of installed product	695.5 mm
Width of installed product	288 mm
Built-in height	695.5 mm
Built-in width	288 mm

**Cover, door**

Material thickness cover	1 mm
Type of door closing	Latch
Number of keylock of the door	0
Door type for switch gear cabinet	Stop door
Door leave	single
Transparent cover or door	Yes

**Materials**

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Equipment**

Number of rows	4
----------------	---

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

Protection index IP	IP30
---------------------	------