



VZ403

**Terminal, Volta, additional terminalm, 1Ph+N**

**Technical properties**

**Architecture**

Number of poles 2 P

**Electric current**

Rated current 63 A

**Dimensions**

Depth of installed product 290 mm

Height of installed product 38 mm

Length 270 mm

Width of installed product 17 mm

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Transparent No

**Connection**

Conductor cross-section (flexible), with wire end sleeve 1.5...25 mm<sup>2</sup>

Conductor cross-section (flexible), without wire end sleeve 1.5...25 mm<sup>2</sup>

Connection cross-section of input and output with screws, for massive conductors 1.5 / 25 mm<sup>2</sup>

Connection cross section of access and exit with screws, for flexible conductor 8 / 15 mm<sup>2</sup>

Type of connection Quickconnect

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

Operating temperature -25...40 °C