



VZ403

**Terminal, Volta, additional terminalm, 1Ph+N**

**Technical properties**

**Architecture**

Number of poles	2 P
Fixing mode	Snap

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Depth of installed product	290 mm
Height of installed product	38 mm
Length	270 mm
Width of installed product	17 mm

**Materials**

Colour	white
RAL colour	RAL 9010 - Pure white
Material	Mixed materials
Transparent	No

**Connection**

Conductor cross-section (flexible), with wire end sleeve	1.5...25 mm <sup>2</sup>
Conductor cross-section (flexible), without wire end sleeve	1.5...25 mm <sup>2</sup>
Connection cross-section of input and output with screws, for massive conductors	1.5 / 25 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	8 / 15 mm <sup>2</sup>
Type of connection	Quickconnect

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------