



VZ604N

Door,golf,white,accessory,for VF/VS212

Technical properties

Architecture

Intended door position	left
------------------------	------

Dimensions

Depth of installed product	16.5 mm
Internal depth	16.5 mm
Height of installed product	375 mm
Width of installed product	280 mm
Built-in height	375 mm
Built-in width	280 mm

Cover, door

Number of keylock of the door	0
Door leave	single
Transparent cover or door	No

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Surface appearance	glossy
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	2
Quantity of section in width	1

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature

-25...40 °C