



VZ607N

**Door,golf,white,accessory,for VF/VS118**

**Technical properties**

**Architecture**

Intended door position left

**Dimensions**

Depth of installed product 16.5 mm

Internal depth 16.5 mm

Height of installed product 250 mm

Width of installed product 388 mm

Built-in height 250 mm

Built-in width 388 mm

**Cover, door**

Number of keylock of the door 0

Door leave single

Transparent cover or door No

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Surface appearance glossy

Type of surface treatment untreated

**Installation, mounting**

Suitable for outdoor use No

**Equipment**

Number of rows 1

Quantity of section in width 1

**Standards**

European directive WEEE not concerned

**Safety**

IK protection code against mechanical impacts IK07

Protection class isol.class II

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

---

Operating temperature

-25...40 °C