



VZ625N

**Door,golf,transparent,accessory,for VF/VS312**

**Technical properties**

**Architecture**

Intended door position	left
Fixing mode	Clamping

**Dimensions**

Depth of installed product	16.5 mm
Internal depth	16.5 mm
Height of installed product	500 mm
Width of installed product	280 mm
Built-in height	500 mm
Built-in width	280 mm

**Cover, door**

Number of keylock of the door	0
Door leave	single
Transparent cover or door	Yes

**Materials**

Colour	transparent
Material	plastic
Type of surface treatment	untreated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Equipment**

Number of rows	3
Quantity of section in width	1

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

IK protection code against mechanical impacts	IK07
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------