



WDI100

IP IP20

Touch Panel 10", Android

Technical properties

Architecture

Fixing mode flush-mounting

Functions

Touch function Yes

Connectivity

Connection RJ45 cable in scope of delivery

Ethernet data rate 10/100 Mbit/s

Voltage

Auxiliary voltage 18...48 V DC

Power over Ethernet (PoE) 18...48 V DC

Dimensions

Assembling height 10 mm

Screen

Resolution graphical display 1280 x 800 px

TFT screen size 10 "

Display yes

Storage

RAM 512 MB

Materials

RAL colour RAL 7016 - Anthracite grey

Material glass

Material family Glass

Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting, for vertical and horizontal mounting

Connection

Conductor cross-section (flexible), with wire end sleeve 0.75 mm²

Settings

Supported configuration modes system

Equipment

Text field No

Light intensity	300 cd/m ²
Processor	1 GHz
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	5...45 °C
Storage/transport temperature	-20...60 °C
Relative humidity (without condensation)	10...90 %
Identification	
Composition	Control element
Main design line	KNX