



WDW070

IP20

## Housing flush-mounted for WDI07x

### Technical properties

#### Architecture

Fixing mode flush-mounting

#### Functions

Touch function No

#### Connectivity

Connection RJ45 cable in scope of delivery

#### Dimensions

Cavity wall opening (W x H x D) 190 x 126 x 47 mm

#### Power

Total power loss under IN 0 W

Dissipated energy in cable 0 W

#### Screen

Display no

#### Materials

RAL colour RAL 7016 - Anthracite grey

Material Steel

Material family Metal

#### Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting, for vertical and horizontal mounting

#### Equipment

Text field No

#### Safety

Protection index IP IP20

#### Use conditions

Storage/transport temperature -20...60 °C

Relative humidity (without condensation) 10...90 %

#### Identification

Composition other

Main design line KNX